

사용설명서

2100 Velocity Meter



SECHANG INSTRUMENTS

.....



Contents

1	3
1.	3
2. 2100	4
3. 2100	4
4. 2100	5
5. 2100	6
6. 2100	7
7. 2100 -	9
2 . 2100-STD, 2100-LX	10
1.	10
2.	10
3. 2100	10
4. (photo-fiber-optic)	11
5. 2100	11

.....

1 .

1 .

25 2100 / / 0.1

(가 5 90 가 가) 가

2100 9 ,
(fiber-optics) 가 (rotor) . 2
(fiber-optics) RPM , ,

2100 (field) , (minor)
. 1 / ,

가 ,

2100 가 , 가

가 .

가 .

Sechang Instruments

2. 2100

2100

1. 6 (1/16")
2. 2100
3. "CALIBRATE" 186(/)
610(/) "FEET/METERS"
4. "COUNT" 가
() 가 .1
4 가 . (.)
5. Min() ("OFF"
)
- 6.
7. "RESET" 0
8. (1.5)
(moving average)" (")


3. 2100

가 ,가 , 가


가 " " ,

ABS , ABS

()



4 .





가

5

5

가

가 "COUNT"

가

가

1

4

(

1

LCD

4

()

)

()

가

"

5 .

2100

2100

가

2100

2100

:

"

2100

2100

(1.5 /

)

(

)

,

,

,

:

2100

1

4

(fiberoptic)

(eyes)



Sechang Instruments

.....

" (count)" 2100 .

10 가 10

가

/ " "

가

가

2100

6 . 2100

2100 "CALIBRATE" .

가 , "FEET/METERS" ()

"FEET" "METERS"

:

FEET = 186
METERS = 610

가 가

9

() 가

: 가 186

가 184 1%가

2100

.....

.....

[(1.5FPS)]

10-20 (Dock)가

"COUNT" "START/STOP" 가

"RESET" 0 . (

.)

6-12 , .

가 가 가

(guide)

, "START/STOP" 가

"START/STOP" 가

가 "RESET" 0

가 , 가 10 가

가 /

2100 가 가

10 x

FEET CAL. No = -----

()

3.281(1)

"CALIBRATE" . "FEET/METERS" ()

"F" , 가 186 /

가 , 가 "CAL ADJUST"

. "CAL ADJUST"

()

()

가 가

9 가

.....

(potentiometer)

가

가

2100

가

가 (

“CALIBRATE” .)

:

()

가

7. 2100 -

OFF & OFF :

VELOCITY :

가

. LCD

“FEET” ” METERS”

/

10 1.5

--- 20 6.0

90 30.0

START/STOP : “COUNT”

” RESET”

RESET : 0

(OFF). “ 0”

(

가

)

“RESET”

”

“

CALIBRATE : LCD 가 “ ”

“FEET/METERS”

COUNT :

가

2100

.....

FEET/METERS : . / , /

CALIBRATION ADJUST : 가
"CALIBRATE"

가 .

2 . 2100-STD, 2100-LX

1 .

. 5/16

가

2 .

(가)

90

1/4

5/16

(foot)

3 . 2100

(

.....

.....

90)
"MIN" 2100
:
가
2100

4 . (photo-fiber-optic)

1. 가
(grease)

2. (boom)

.()

3. 가 가
가

4. 가

5 . 2100

2100 가

/

가
2100 1/16

2100

1. (leading edge)

150 grit

가

.....



2. 2 / 가

3. 2100 (canned air)
(2100-A27) (bore)
(grease)


4. (2100-A21)
가
(spin test)
"COUNT"
가 가 "RESET"
가

5. 가 (buzz)
(2100-A27) (2100-A26)
가
3FPS

6. (trust-bearing) (2100-A23)
() "cup" (가
) 2100-A23 2FPS
2100

7. (photo-optics)
(eyes)
가 (2100-A27)
(fiber optics) (eyes)
2100 2100





1518


(4Meter)



2100
Velocity Meter



1 : 1998 4 6



121-884

364-38

TEL : 332-7511 ()

FAX : 332-5912 ()



e-mail : sechang@sechang.com

Internet Website : <http://www.sechang.com>